| UNIT CLOSED CIRCUIT COOLER   |   |  |   | EVADOO I  | NC  | eva                    | pco                       | DWG. #   | WB3241414-DRC-S   | ST.    | REV.            |
|--|---|--|---|---|---|------------------------|---------------------------|----------|-------------------|--------|-----------------|
| MODEL #  | ATWB 24-7N14  | SCALE NTS  |   | EVAPCO, I   | NC.   |                        |                           | SERIAL # |                   |        | DATE 11/6/2025  |
| 2. HEAVIE<br>3. MPT DE<br>FPT DE<br>BFW DI<br>GVD DE<br>FLG DE<br>PE DEN<br>4. +UNIT V.<br>20 psi M<br>6. *-APPR<br>FOR PF<br>PIPING<br>7. 3/4" [19<br>RECOM | N MOTOR LOCATION EST SECTION IS UPPER ENOTES MALE PIPE THE ENOTES FEMALE PIPE TO ENOTES BEVELED FOR ENOTES FLANGE HOTES PLAIN END WEIGHT DOES NOT INC SORIES (SEE ACCESSO JP WATER PRESSURE MIN [137 kPa], 50 psi MAX OXIMATE DIMENSIONS RE-FABRICATION OF CO mm] DIA. MOUNTING HO MIMENDED STEEL SUPP SIONS LISTED AS FOLL ENGLISH FT-IN METRIC [mm] | READ THREAD WELDING CLUDE DRY DRAWINGS) X [344 kPa] DO NOT USE DNNECTING OLES. REFER TO ORT DRAWING. |   |   |   | <u>PL</u>              | FACE B                    |          | (2) ACCESS DOOR   | FACE D |                 |
|  |   |  |   |   | 7"<br>[ 178   | ]                      | 1'-3 1/4"<br>[ 387 ]      | <u> </u> | ACE A             |        |                 |
|  | 3'-11 3/4" *  | (2) 2" [50] MPT MAKE-UF  (2) 3" [80] MPT DRAIF   | UT (4) 4                                | 5'-9 1/4" * 3'-3/8" * [ 924] *  "(100] BFW FLUID IN  "(100] BFW FLUID OUT  "(100] BFW FLUID OUT  "(154] *  11'-4 3/4" [ 13473]  11'-5 3/4" [ 1422]  11'-10" [ 3607] | 10'-5 1/8"<br>[ 3180 ]<br>7'-2 1/4"<br>[ 2189 ]<br>1'-5"<br>[ 433 ] | 17'-7 3/8"<br>[ 5369 ] | (4) 1/2° [15]<br>FPT VENT |          | '-11 3/4"<br>4261 |        |                 |
|  | -   |  | 24'-1 1/8"<br>[ 7344 ]<br><b>FACE B</b> | -   |   |                        | [ 470]                    |          | 4261] ACE A       |        |                 |
| SHIPPING<br>WEIGHT   | 55400 lbs+  | [25130] kg+  | OPERATING<br>WEIGHT                     | 83240 lbs+ [37760] kg+  | HEAVIEST SEC<br>WEIGHT  | TION                   | 24640 lbs+ [11180] kg+    | NO. OF   | SHIPPING SECTIONS | 4 D    | RAWN BY:<br>SLR |