



UNIT	COOLING TOWER		EVAPCO, INC. 	DWG. #	T4282424-DRA-ST	REV.
MODEL #	AT 228-2024	SCALE NTS		SERIAL #		DATE 2/20/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT
DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]



FACE B



FACE A

SHIPPING WEIGHT 33460 lbs+ [15180] kg+ OPERATING WEIGHT 66100 lbs+ [29985] kg+ HEAVIEST SECTION WEIGHT 11170 lbs+ [5070] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: MER