UNIT	COOLING TOW	/ER	EVADOO THE EVEDED	DWG. # T3144848-DRC-GDST	REV.
MODEL #	AT 214-4R48	SCALE NTS	EVAPCO, INC. evapco	SERIAL #	DATE <sub>11/22/2025</sub>
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING		AD READ	FACE C		
GVD DE FLG DEI 4. +UNIT V ACCESS 5. MAKE-U 20 psi M 6. 3/4" [19I RECOM 7. DIMENS	NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLU SCHES (SEE ACCESSOR' IP WATER PRESSURE IIN [137 KPa], 50 psi MAX [3 MM] DIA. MOUNTING HOL ENDED STEEL SUPPORT SIONS LISTED AS FOLLOV IGLISH FT-IN ETRIC] MM	IDE Y DRAWINGS) 844 kPa]	ACCESS DOOR  FACE B  PLAN VIEW		FACE D  ACCESS DOOR
			FACE A	<u>A</u>	
Tr	<del></del>	7" [ 178]	1'-5 1/4" [ 438 ]		
	ACCESS MOOR	10  11 2 4	11'-10 1/2"	(%)	
		10'-11 3/4" [ 3345] 	(2) 14" [350] BFW/GVD	0	
		8'-3 3/8" [ 2523 ]	13'-3 7/8" [4061]		
			2'-2" [ 659 ]	(2) 4 [100] FPT (2) 3" [80] MPT OUTLET MAKE-UP (2) 4 [100] FPT OVERFLOW	
	13'-11 1/4"	3/8" [10]	[ 103 ] - 23'-9" [ 7239]	2 1/2" [64]	
Γ-	[ 4248'] <b>FACE B</b>	[ 10]	47'-8 1/ [ 14542 FACE A		-

HEAVIEST SECTION WEIGHT

14100 lbs+ [6400] kg+

SHIPPING WEIGHT OPERATING WEIGHT

72120 lbs+ [32715] kg+

39640 lbs+ [17985] kg+

DRAWN BY: JLG

NO. OF SHIPPING SECTIONS