INIT COOLING TOWER				/A DCO T	NC PV		DWG. #	T4285260-DRA-ST	REV.
10DEL #	AT 428-5N52	SCALE NTS	T EV	APCO, I	NC.		SERIAL #		DATE _{12/13/2025}
2. HEAVI 3. MPT D FPT D BFW D GVD D FLG D PE DE 4. +UNIT ACCE: 5. MAKE: 20 psi 6. 3/4" [1 REFEE DRAW 7. DIMEN [MI 8. PAN F EVAPC BY OT 9. PAN E	NSIONS LISTED AS FOLLOW IGLISH FT-IN ETRIC] [mm] LUME BOX EQUALIZERS SU CO. PAN EQUALIZER PIPING	DE DE DRAWINGS) 44 kPa] S. L SUPPORT S: IPPLIED BY IS SUPPLIED		FACE B		(8) ACCESS DOOR			FACE D
(4) 4	13 (100) MPT / (10	11'-6" 3505] -11',4" 3994] -51/2" 4102] -61/2" 4128] 111,1/4"	1'-3 1/4" [387] 6'-11 5/8" [2124] 16'-3 3/4" [4972] 2'-2" [660] 1'-5 3/8" [441] 9" [229] 4" [102]	12'-1/4" [3664] -3 1/2" 5794] 10'-3 1/4" [3131]	25'-9 [7849	9 1/8" [232] 1 3/8" [35]	(4) 12" BFW/GV (SEE NO	/D EQUALIZER	2" [51]
FACE A FACE B									
SHIPPING 99880 lbs+ [45305] kg+ WEIGHT		OPERATING 16 WEIGHT	66440 lbs+ [75500] kg+	HEAVIEST SECTION WEIGHT	18140 lbs+ [8230] kg+	NO. OF SHI	PPING SECTIONS 8	DRAWN BY: MER	