INIT COOLING TOWER				/ADCO T	NC PV	anco e	DWG. #	T4285260-DRA-ST	REV.
10DEL #	AT 428-5O52	SCALE NTS		VAPCO, I	NC.		SERIAL #		DATE _{12/14/2025}
2. HEAV 3. MPT I FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. 3/4" [1 REFEI DRAW 7. DIMEN [M 8. PAN F EVAP BY OT 9. PAN E	AN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES BEVELED FOR WID DENOTES BEVELED FOR WID DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLUIT SSORIES (SEE ACCESSORY -UP WATER PRESSURE MIN [137 KPa], 50 psi MAX [3 9MM] DIA. MOUNTING HOLE R TO RECOMMENDED STEE VING NSIONS LISTED AS FOLLOW NGLISH FT-IN ETRIC] [mm] FLUME BOX EQUALIZERS SL CO. PAN EQUALIZER PIPING THERS. EQUALIZER NIPPLE IS 11'-10 EACH STEP SIDE.	DE / DRAWINGS) 44 kPa] 5. L SUPPORT 7. S: JPPLIED BY 6 IS SUPPLIED		FACE B PLAN VIEW		(8) ACCESS DOOR			FACE D
(4) 4	13 (100) MPT / (130) MPT / (13	11'-6" 3505] -1 1/4" 3994] -5 1/2" 4102] -6 1/2" 4128] 11 1/4"	1'-3 1/4" [387] 6'-11 5/8" [16'-3 3/4"	7" [178] 12'-1/4" [3664] 2'-3 1/2" [51] 10'-3 1/4" [3131]	25'-9	9 1/8" [232] 1 3/8" [35]	(4) 12" BFW/GV (SEE NO	[300] /D EQUALIZER DTE #9)	2" [51]
FACE B						<u>FACE A</u>	1		
SHIPPING 99960 lbs+ [45345] kg+ WEIGHT		OPERATING 1 WEIGHT	166520 lbs+ [75535] kg+	HEAVIEST SECTION WEIGHT	18160 lbs+ [8240] kg+	NO. OF SHI	PPING SECTIONS 8	DRAWN BY: MER	