UNIT COOLING TOWER			EVAPCO, INC. Evapeo				DWo	G. # T312402	REV.		
MODEL #	AT 212-2N40	SCALE NTS	EVAPC	O, INC	1	<b>P</b>	SER	IAL #		DATE 11/21/2025	
2. HEAN 3. MPT FPT I BFW GVD FLG 4. +UNI ACKI 20 ps 6. 3/4" [ RECC 7. DIME	FAN MOTOR LOCATION VIEST SECTION IS UPPER S DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THI DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE T WEIGHT DOES NOT INCLU ESSORIES (SEE ACCESSOR E-UP WATER PRESSURE SI MIN [137 kPa], 50 psi MAX [19MM] DIA. MOUNTING HOL OMENDED STEEL SUPPOR ENSIONS LISTED AS FOLLO ENGLISH FT-IN [METRIC] [mm]	EAD READ VELDING  JDE LY DRAWINGS)  344 kPa] LES. REFER TO T DRAWING.	FACE B PLAN VIEW		ACCESS DOO	FACE	EC	ACCESS	DOOR	FACE D	
				FACE A							
		7" [ 178	] 1'-3 1/4" — [ 387 ]		23						
		2" [ 51 ] 8'-4" [ 2540 ]	T   T   T   T   T   T   T   T   T   T	10'-0"	(M)			(M)	) 10" [250] W/GVD		
		7'-2 1/4" [ 2191 ]	5 1/4" 731 ] 10'-1" [ 3073 ]								
			2'-1 1/4"	[ 3048 ]	19'-3" [ 5867 ] 19'-6 3/4" [ 5963 ] 20'-0" [ 6096 ]		(2) 3" [80] F OVERFLOW (2) 3" [80] F DRAIN (2) 2" [50] MPT MAKE-UP 2 1/2" [ 64 ]	PT (2) 1 BFW) PT OUTL	0" [250] /GVD LET		
	11'-10" [ 3607 ] FACE B	3/8" [9]	( )= 1	-	[ סהאס	40'-2 [ 122 <b>FACE</b>	1/2" 56 ]		•	_	
SHIPPING WEIGHT		10790] kg+	OPERATING 44580 lbs+ [202	225] kg+	AVIEST SECTION WEIGHT	7630 lbs+ [346	65] kg+	NO. OF SHIPPING SEC	TIONS 4	DRAWN BY: BLL	