UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-3N36

EVAPCO, INC. Evapco



DWG. # REV. WB3243606-DRC-ST DATE<sub>11/11/2025</sub> SERIAL #


DRAWN BY:


## NOTES:

**SHIPPING** 

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]






82600 lbs+ [37470] kg+

**OPERATING** 

WEIGHT

134560 lbs+ [61040] kg+



16580 lbs+ [7525] kg+

NO. OF SHIPPING SECTIONS

HEAVIEST SECTION

WEIGHT