| NIT COOLING TOWER | EV | EVAPCO, INC. Evapeo | | | DWG. # CT4C071248-D | | -ST | REV. |
|--|-------------------------------------|--|---|---|-----------------------------------|------------------|--------|----------------------------|
| 10DEL # AT 17-4H12 SCALE N | E V | APCO, II | YC. | 9 | SERIAL # | | | DATE _{12/15/2025} |
| NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] | | 1'-2" 356] | FACE B PLAN VIEW | | FACE A | ACCESS DOOR | FACE I | <u>0</u> |
| 1'-9 3/8" [543] 8" [200] BFW/GVD INLET | 3'-8" | 9'-7 3/8" 2" [50] MPT [2929] | 2'-11 3/8" [899] 6'-5 1/8" 13'-8 3/8" [4176] 2" [51] | | | | | |
| 3" [80] MP' OVERFLOV 8" [20] | 41/ | 3" [80] MPT DRAIN 4" 1'-11 1/8" 7] 1'-12 1/8" | 4'-3 7/8" [1318] 1 3/8" [35] | | | | | |
| | 3'-1 3/4" [959] 7'-4" CE B | 7 1/2" 0] | HEAVIEST SECTION 3740 WEIGHT | | 11'-11 3/4" [3651] FACE A | HIPPING SECTIONS | 2 DR | ^{AWN BY:} MBG |