JNIT		•	DWG. #	REV
COOLING TOWER	EVAPCO, IN	Evapco	CT4C072848-DRA-ST	- DATE:
AT 27-4I28 SCALE NTS	LVAI CO, II		SERIAL#	11/21/2025
NOTES:  1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]	FACE B PLAN VIEV	(M) ACCESS DOC		FACE D
1'-9 3/8" [543]	1'-2" [355]	398] Access Door Look	Acceptable (M)	ES R R
(2) 8" [200] / M BFW/GVD INLET (2)	6'-5 1/8" [12') 2" [50] MPT	2" [51]		
(2) 3" [80] MPT	8]	[35]————————————————————————————————————	2 1/2" [64] 28'-2" [8585]	P

HEAVIEST SECTION WEIGHT

20170 lbs+ [9150] kg+

OPERATING WEIGHT

SHIPPING WEIGHT

12320 lbs+ [5590] kg+

4160 lbs+ [1890] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG