UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapeo		evapco	DWG. # WB3TM2414-DRC-ST	REV
MODEL #	ATWB 10-7I24	SCALE NTS	EVAP	CO, INC.		SERIAL #	DATE <sub>11/22/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS UPPER SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  5. MAKE-UP WATER PRESSURE 20 psi MIN [137 KPa], 50 psi MAX [344 KPa]  6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING  7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.			<u></u>	FACE B PLAN VIEW	ACCESS DOOR	ACCESS DOOR	FACE D
8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN					<u>FAC</u>	<u>E A</u>	
	METRIC [mm]		7" [ 178]				
	<del>[</del>	<del></del>	<u> </u>	1'-3 1/4" [ 387 ]			
	3'-11 3/4" * (4) 4* [100] BFW (4) 4* [100] BFW	O FLUID IN	[-6 3/8" * 10'-5 1/8" [ 3180 ] 16'-7 3/8" [ 5064 ]	(4) 1/2" [15] FPT VENT		(A)	
1	2) 2" [50] MPT MAKE-UP (2) 3" [80]		6"-2 1/4" [ 154] * 6'-2 1/4" [ 1884] 1'-5" 433]				
	[ 92 ] - 5 1/4" [ 133 ] - 4 1/4" [ 108 ] - 5'-11 3/4 [ 1822 ]		2) 3" [80] MPT WERFLOW	1'-5" [ 432 ]	11'-11 3/4" [ 3651 ] 24' [ 73	2 1/2" [ 64] -2"	1'-5" [ 432]

FACE B

**FACE A**