UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 17-6K14

EVAPCO, INC. Evapeo




DWG. # REV. WB3171412-DRD-ST DATE<sub>11/18/2025</sub> SERIAL #


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

## **FACE C**



## **FACE** A





**SHIPPING** WEIGHT

33980 lbs+ [15415] kg+

**OPERATING** WEIGHT

50540 lbs+ [22925] kg+

HEAVIEST SECTION WEIGHT

14980 lbs+ [6795] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: