

CLOSED CIRCUIT COOLER	EVADOO TNO EVEDO	DWG. # WB3122014-DRC-ST	REV.
ODEL # ATWB 12-7O20 SCALE NTS	EVAPCO, INC. Evapeo	SERIAL #	DATE <sub>11/20/202</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	FACE B PLAN VIEW	FACE C  ACCESS DOOR  FACE D  FACE A	<u>.</u>
	7" [ 178 ]		





 
 SHIPPING WEIGHT
 38620 lbs+ [17520] kg+
 OPERATING WEIGHT
 58560 lbs+ [26565] kg+
 HEAVIEST SECTION WEIGHT
 34110 lbs+ [15475] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY: SLR