CLOSED CIRCUIT COOLER				FV/A DC/	^		vanca	DWG.	# WB3122006-DR0	C-SF	REV.
10DEL #	ATWB 12-3N20-Z	SCALE NTS		EVAPC	J, II	VC.		SERIA	L #		DATE 11/21/2025
2. HÉAVIE 3. MPT DE FPT DE FPT DE GVD DE FLG DE PE DEN 4. + UNIT \ ACCES FOR AG 5. MAKE-L 20 psi M 6. * - APPF FOR PR PIPING 7. SERIES 3. 3/4" [19] RECOM	S FLOW PIPING AND AUX. C BY OTHERS MM] DIA. MOUNTING HOLE IMENDED STEEL SUPPORT	DE DE DRAWINGS 44 kPa] O NOT USE ECTING CROSSOVER S. REFER TO DRAWING.		PLAN V	FACE B			FACE C	CESS DOOR	FAC	CE D
). DIMENS	SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	S:		7"			,	FACE A			
				7" [178]		1'-3 1/4" [387]					
	JCI						JCI			7	
	(4) 4" [100] BFW FLUID IN	5'-9 1/4" *	3'-	.3/8" * 24]	(4 F	i) 1/2" [15]					
	1'-10 1/4" * [565]		(4) 4" FLUII	[100] BFW O OUT 14'-5 7/8" [4416]	SERIES FLOW P (SEE NOTE						
	2" [50] MPT — MAKE-UP — 2'-1 1/4" [643]			6" * 6'-2 1/4" [1884] 1-5" [433]	AUX. CROSSOV (SEE NOT	ER DRAIN —				-	
	3 5/8" _ DRAI	0] MPT IN 3" [1/4" OVE 133]	[80] MPT ERFLOW	T							
	4 1/										
	[2	":-2" 184]				2'-1/2" [622]	-	20'-0" _	-		
		FACE B					,	FACE A			
SHIPPING WEIGHT	22570 lbs+ [10	240] kg+	OPERATING WEIGHT	37040 lbs+ [16805]	kg+	HEAVIEST SECTION WEIGHT	18060 lbs+ [8195]	kg+	NO. OF SHIPPING SECTIONS	2 DR	AWN BY: JLG