UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-7N14-Z

EVAPCO, INC. Evapco



DWG. # REV. WB3241414-DRC-SF DATE 11/6/2025 SERIAL #


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. \*-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



**PLAN VIEW** 

**FACE C** 



**FACE B** FACE D

## 5'-9 1/4" [ 1759] 3'-3/8" \* [ 924] (8) 4" [100] BFW FLUID IN 10'-5 1/8" [ 3180 ] (8) 4" [100] BFW 3'-11 3/4" \* [ 1213 ] FLUID OUT 17'-7 3/8" 6" [ 154] 7'-2 1/4' [ 2189] 2'-1 1/4' 3 5/8" [ 92] 11'-4 3/4' [ 3473] (2) 3" [80] MPT -DRAIN 11'-5 3/4' [ 3499 ] (2) 3" [80] MPT OVERFLOW 11'-10" [ 3607]

**FACE A** (8) 1/2" [15] FPT VENT SERIES FLOW PIPING SEE NOTE 7 AUX. CROSSOVER DRAIN SEE NOTE 7 13'-11 3/4' [ 4261] FACE A

**SHIPPING** 55400 lbs+ [25130] kg+ WEIGHT

OPERATING WEIGHT

**FACE B** 

83240 lbs+ [37760] kg+

HEAVIEST SECTION WEIGHT

24640 lbs+ [11180] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG