UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-6N24-Z

EVAPCO, INC. evapco





DWG. # REV. WB3242412-DRD-SF DATE 11/8/2025 SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [MM]

FACE C







DRAWN BY: JLG NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 18690 lbs+ [8480] kg+ 85940 lbs+ [38985] kg+ 130200 lbs+ [59060] kg+ WEIGHT WEIGHT WEIGHT