| UNIT | CLOSED CIRCUIT COOLER | |
|---------|-----------------------|-----------|
| MODEL # | ATWB 3-5D3-7 | SCALE NTS |

EVAPCO, INC. evapco



DWG. # REV. WB3030310-DRE-SF DATE 11/5/2025 SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] MM





FACE C

FACE B **PLAN VIEW**



FACE A





DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 1610 lbs+ [735] kg+ 2270 lbs+ [1030] kg+ 1330 lbs+ [605] kg+ WEIGHT WEIGHT WEIGHT