



NOTES:

- |   |  |         |       |  |                  |
|---|--|---------|-------|--|------------------|
| <ol style="list-style-type: none"><li>1. BEAMS SHOULD BE SIZED IN ACCORDANCE WITH ACCEPTED STRUCTURAL PRACTICES. MAXIMUM DEFLECTION OF BEAM UNDER UNIT TO BE 1/360 OF UNIT LENGTH NOT TO EXCEED 1/2" [13mm].</li><li>2. DEFLECTION MAY BE CALCULATED BY USING 55% OF THE OPERATING WEIGHT AS A UNIFORM LOAD ON EACH BEAM. SEE CERTIFIED PRINT FOR OPERATING WEIGHT.</li><li>3. SUPPORT BEAMS AND ANCHOR HARDWARE ARE TO BE FURNISHED BY OTHERS. ANCHOR HARDWARE TO BE ASTM A325 5/8" [16mm] BOLT OR EQUIVALENT.</li><li>4. BEAMS MUST BE LOCATED UNDER THE FULL LENGTH OF THE PAN SECTION.</li><li>5. SUPPORTING BEAM SURFACE MUST BE LEVEL. DO NOT LEVEL THE UNIT BY PLACING SHIMS BETWEEN THE UNIT MOUNTING FLANGE AND THE SUPPORTING BEAM.</li></ol> | <p>CONSULT THE FACTORY FOR ALTERNATE SUPPORT CONFIGURATIONS.</p> <ol style="list-style-type: none"><li>7. UNIT SHOULD BE POSITIONED ON STEEL SUCH THAT THE ANCHORING HARDWARE FULLY PENETRATES THE BEAM'S FLANGE AND CLEARS THE BEAM'S WEB.</li><li>8. WHEN VIBRATION ISOLATION IS REQUIRED, THE VIBRATION ISOLATORS (BY OTHERS) MUST BE LOCATED UNDER THE SUPPORTING BEAMS AND NOT BETWEEN THE SUPPORTING STEEL BEAMS AND THE UNIT.</li><li>9. DIMENSIONS LISTED AS FOLLOWS:</li></ol> <table border="0" style="width: 100%;"><tr><td style="text-align: right;">ENGLISH</td><td style="text-align: center;">FT-IN</td></tr><tr><td></td><td style="text-align: center;">[METRIC]    [mm]</td></tr></table> | ENGLISH | FT-IN |  | [METRIC]    [mm] |
| ENGLISH   | FT-IN  |         |       |  |                  |
|   | [METRIC]    [mm]   |         |       |  |                  |