


UNIT <b>CLOSED CIRCUIT COOLER</b>		<b>EVAPCO, INC.</b> 	DWG. # WB36M2412-DRC-SF	REV. -
MODEL # ATWB 20-6M24-Z	SCALE NTS		SERIAL #	DATE 7/4/2025


  

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

**FACE B**



**FACE C**


(4) ACCESS DOOR

**FACE D**

**FACE A**

**FACE B**



16 4" [100] BFW FLUID IN

3'-11 3/4" \* [1213]

2'-1 1/4" [643]

1'-5" [433]

3 5/8" [92]

(4) 3" [80] MPT OVERFLOW

(4) 2" [50] MPT MAKE-UP

(4) 3" [80] MPT DRAIN

5 1/8" [130]

20'-5/8" [6112]

4'-9" [1448] \*

2'-6 3/8" \* [772]

10'-5 1/8" [3180]

18'-7 3/8" [5674]

6" [154] \*

8'-2 1/4" [2494]

3'-10" [1168]

9'-4 1/2" [2858]

9'-5 1/2" [2883]


9'-9 3/4" [2991]

16 4" [100] BFW FLUID OUT

**FACE B**

**FACE A**



1'-3 1/4" [387]

16 1/2" [15] FPT VENT

SERIES FLOW PIPING (SEE NOTE 7)

AUX. CROSSOVER DRAIN (SEE NOTE 7)

1'-5" [432]

24'-2" [7366]

1'-5" [432]

**FACE A**

SHIPPING WEIGHT	73580 lbs+ [33380] kg+	OPERATING WEIGHT	111480 lbs+ [50570] kg+	HEAVIEST SECTION WEIGHT	15690 lbs+ [7120] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SLR
-----------------	------------------------	------------------	-------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----