NOTES:  1. (M) - FAN MOTOR LOCATION  2. HEAVIEST SECTION IS UPPER SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES FLANGE PE DENOTES PLAIN END  4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)  5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING	FACE B PLAN VIEW	FACE C  ACCESS DOOR  FACE	DATE <sub>11/21/2025</sub>
1. (M) - FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES FLANGE PE DENOTES PLAIN END 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING	FACE B PLAN VIEW	ACCESS DOOR	<u>D</u>
7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS 9. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.		FACE A	
10. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]  7" [ 178]	1'-3 1/4"		
5'-9 1/4" * 3'-3/8" * 10'-5 1/8 [ 3180 ]	(4) 1/2" [15] FPT VENT  1-7 3/8" SERIES FLOW PIPING (SEE NOTE 7)	(*)	
2" [50] MPT 6" - 154] * 6'-2 1/4' [1884]  2'-1 1/4" [643] 3 5/8" 3" [80] MPT OVERFLOW  OVERFLOW	AUX. CROSSOVER DRAIN (SEE NOTE 7)		
DRÁIN OVÉRFLOW  5 1/4" [ 133]  4 1/4" [ 108]  7'-2" [ 2184]  11'-10" [ 3607]	1'-11 1/8" [ 587]		

SHIPPING WEIGHT 30830 lbs+ [13985] kg+ OPERATING WEIGHT 47450 lbs+ [21525] kg+ HEAVIEST SECTION WEIGHT 26910 lbs+ [12210] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG