JNIT	CLOSED CIRCUIT CO	OOLER	EVADOO T	NC EV		WG. # WB3122008-DRC	-SF REV
10DEL #	ATWB 12-4N20-Z	SCALE NTS	EVAPCO, I	NC.	S	ERIAL #	DATE 11/21/2025
2. HÉAVIES 3. MPT DEI FPT DEN BFW DE GVD DE FLG DEN PE DENI 4. + UNIT V ACCESS 5. MAKE-U 20 psi MI 6. * - APPR FOR PRI PIPING 7. SERIES 3.3/4" [19N RECOMI	N MOTOR LOCATION ST SECTION IS UPPER SEC NOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES BEVELED FOR WE NOTES GROOVED NOTES FLANGE OTES PLAIN END VEIGHT DOES NOT INCLUI SCESSORIES) P WATER PRESSURE IN [137 kPa], 50 psi MAX [34 COXIMATE DIMENSIONS DO E-FABRICATION OF CONNI FLOW PIPING AND AUX. C BY OTHERS MM] DIA. MOUNTING HOLES MENDED STEEL SUPPORT	DE EAD ELDING  DE DRAWINGS  14 kPa] D NOT USE ECTING  CROSSOVER  S. REFER TO DRAWING.	FACE B PLAN VIEW		FACE C	ACCESS DOOR	FACE D
). DIMENS	IONS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	S:	7" [ 178] ]	1'-3 1/4" [ 387 ]	FACE A		
	JC <u> </u>			13871		==51	
	(4) 4" [100] BFW FLUID IN	5'-9 1/4" *	3'-3/8" * [ 924 ] 9'-1/8" [ 2748 ]	(4) 1/2" [15] — FPT VENT		(M)	
	2'-6 3/4" * [781]		(4) 4" [100] BFW FLUID OUT 15'-2 3/8" [4632]				
	2" [50] MPT — MAKE-UP — 2'-1 1/4" — [643]		6" * SERIES FLO (SEE NO SEE)  6'-2 1/4" [ 1884]  1'-5" [ 433]	W PIPING — DTE 7)  EVER DRAIN			
	3 5/8" DRA	3" [80] MI 5 1/4" 1133] 1/4" 08]	PT N				
		7'-2" 2184] — [11'-10"	-	2'-1/2" -	20'-0 [ 6096	.]	
SHIPPING WEIGHT	26350 lbs+ [119	FACE B  955] kg+  OPER WEI		HEAVIEST SECTION WEIGHT	21840 lbs+ [9910] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: JLG