DWG. # REV. UNIT **CLOSED CIRCUIT COOLER** WB36M3614-DRC-SF EVAPCO, INC. Evapco DATE_{11/12/2025} MODEL # SERIAL # NTS ATWB 20-7M36-Z NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FACE C FPT DENOTES FEMALE PIPE THREAD (4) ACCESS DOOR BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE **FACE B FACE D** FOR PRE-FABRICATION OF CONNECTING **PIPING PLAN VIEW** 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS. 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm] **FACE A** __ [7" _ [178] 4'-9" 1448] 2'-6 3/8" * (16) 4" [100] BFW M (16) 1/2" [15] FLUID IN FPT VENT 10'-5 1/8' [3180] (16) 4" [100] BFW 3'-11 3/4" [1213] FLUID OUT 18'-7 3/8' SERIES FLOW PIPING -(SEE NOTE 7) 6" [154] AUX. CROSSOVER DRAIN -(SEE NOTE 7) 8'-2 1/4' [2494] 2'-1 1/4" 3'-10" [1168] (4) 2" [50] MPT MAKE-UP 9'-4 1/2" 1'-5" [433] 2858 (4) 3" [80] MPT -DRAIN

5 1/8" [130]

FACE B

3 5/8' [92]

(4) 3" [80] MPT OVERFLOW

9'-5 1/2' [2883]

9'-9 3/4' [2991]

FACE A

25970 lbs+ [11780] kg+

1'-11 1/4" [591]