INIT CLOSED CIRCUIT COOLER		COOLER	EVAPCO, INC. Evapeo		DWG. # CW4C071806-DRA-SF	REV.
10DEL #	ATWB 7-3H18-Z	SCALE NTS	EVAPCO, INC		SERIAL #	DATE 11/4/2025
2. HÉAVI 3. MPT DEFPT D	AN MOTOR LOCATION EST SECTION IS FAN/CAS ENOTES MALE PIPE THR ENOTES FEMALE PIPE THR ENOTES BEVELED FOR N DENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCL SSORIES (SEE ACCESSOF -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX ROXIMATE DIMENSIONS D RE-FABRICATION OF CON S S FLOW PIPING AND AUX I BY OTHERS. 9MM] DIA. MOUNTING HOI MMENDED STEEL SUPPO ISIONS LISTED AS FOLLO ENGLISH FT-IN METRIC [mm]	EAD IREAD VELDING  UDE RY DRAWINGS)  [344 kPa] DO NOT USE INECTING  . CROSSOVER LES. REFER TO RT DRAWING.	FACE B PLAN VIEW	ACCESS	FACE C  DOOR  ACCESS D  FACE A	FACE D
(2) 4 FLU 2"   2"	100] BFW 1-7 1/2" * [495] *  50] MPT MAKE-UP 50] MPT DRAIN  1-11 1/8" [587]  3" [76]		2'-11 3/8" [899]  - 1'-10 7/8" *	3356 1	[18'-0" [5486] FACE A	
SHIPPING WEIGHT	13970 lbs+ [	6340] kg+	OPERATING 19260 lbs+ [8740] kg+ HEAVIEST WEIGHT		NO. OF SHIPPING SECTIONS 2	RAWN BY: TAM