UNIT CLOSED CIRCUIT COOLER			*************************************			DWG. # CIALCOTTON DDA CE REV.	
IODEL #	ATWB 7-4J18-Z	SCALE NTS	EVAPO	CO, INC.	evapco	CW4C071808-DRA-SF SERIAL #	DATE _{10/28/2025}
2. HÉAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DE! 4. +UNIT' ACCES 5. MAKE-I 20 psi N 6. *-APPR FOR PI PIPING 7. SERIES DRAIN 8. 3/4" [19 RECON 9. DIMEN E	IN MOTOR LOCATION EST SECTION IS FAN/CAS ENOTES MALE PIPE THRE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUS ESORIES (SEE ACCESSOR UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [138 kPa], 50 psi MAX [1	EAD READ READ VELDING JDE LY DRAWINGS) 344 kPa] O NOT USE NECTING CROSSOVER ES. REFER TO RT DRAWING.		FACE B PLAN VIEW	ACCESS	FACE C ACCESS FACE A	FACE D
2" [50] MAR 2" [50] D - 1'-1 [5	00) BFW 1 1 1 1 1 1 1 1 1	(4) 4 F	2'-11 3/8" ['-10 7/8" * [899] ['581] *	SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7)			
	-	'-4" 235] CE B		1'-4 7/8" [429]	-	18'-0" [5486] FACE A	

HEAVIEST SECTION WEIGHT

13330 lbs+ [6050] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM

SHIPPING WEIGHT OPERATING WEIGHT

22380 lbs+ [10155] kg+

16350 lbs+ [7420] kg+