INIT CLOSED CIRCUIT COOLER			T		*	DWG.	* CW4C072406-DRA-ST	REV.
10DEL #	ATWB 7-3J24	SCALE NTS	⊢ EV	/APCO, II	VC. Evapeo	SERIAL		DATE 11/1/2025
2. HEAVIE: 3. MPT DE FPT DEI BFW DE GVD DE FLG DEI PE DEN: 4. +UNIT W ACCESS 5. MAKE-U 20 psi M 6. *-APPRC FOR PR PIPING 7. 3/4" [19n RECOMI	I MOTOR LOCATION ST SECTION IS FAN/CASI NOTES MALE PIPE THRE NOTES FEMALE PIPE THRE NOTES BEVELED FOR W NOTES GROOVED NOTES FLANGE OTES PLAIN END VEIGHT DOES NOT INCLL SORIES (SEE ACCESSOR P WATER PRESSURE IN [137 kPa], 50 psi MAX [3 DXIMATE DIMENSIONS DO E-FABRICATION OF CONI nm] DIA. MOUNTING HOL MENDED STEEL SUPPOR IONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ READ FELDING JDE Y DRAWINGS) 344 KPa] D NOT USE NECTING ES. REFER TO RT DRAWING.		FACE B PLAN VIEW	ACCESS DOOR FAC		ACCESS DOOR	FACE D
(2) 2" [50] MAKE- (2) 2" [50] 1'-11 1/s [587]	1-7 1/2" * (4) 4" [100] BFW (4) 4" [100] BFW (4) 4" [100] BFW (4) 4" [100] BFW (4) A" [100] BTW (4) A" [100]	FLUID IN FLUID OUT 11-3 [38	5 1/4" * [133] * 5'-1/4" [1530]	1'-2" [356] (4) 1/2* [15] FPT VENT [570]	11'-11 3/4" [3651]	2 1/ [6 ² -2" -66]	_	1'-5 1/8" [435]
SHIPPING WEIGHT	18540 lbs+ [84	l10] kg+	OPERATING 2 WEIGHT 2	5520 lbs+ [11580] kg+	HEAVIEST SECTION 7370 lbs+ [3345] kg+	+ N	O. OF SHIPPING SECTIONS 4	DRAWN BY: TAM