UNIT	CLOSED CIRCUIT COOLER		
MODEL#	ATWB 7-3J14-Z	SCALE	NTS


EVAPCO, INC. Evapeo

CW4C071406-DRA-ST	REV	-
SERIAL#	DATE:	
		11/1/2025

NOTES


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]






FACE D

FACE A





FACE B FACE A

 SHIPPING WEIGHT
 10570 lbs+ [4795] kg+
 OPERATING WEIGHT
 14570 lbs+ [6610] kg+
 HEAVIEST SECTION WEIGHT
 8380 lbs+ [3805] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY:
 JLG