CLOSED CIRCUIT COOLE			TNIC	evapeo	DWG.# CW4C141414-DRB-ST	REV -	
ATWB 14-7L14	SCALE NTS		EVAPCO,	TINC.		SERIAL#	DATE: 11/19/2025
NOTES 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CA 3. MPT DENOTES MALE PIPE THE FPT DENOTES FEMALE PIPE T BFW DENOTES BEVELED FOR GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INC ACCESSORIES (SEE ACCESSO 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MA) 6. *-APPROXIMATE DIMENSIONS FOR PRE-FABRICATION OF CO PIPING 7. 3/4" [19mm] DIA. MOUNTING HO RECOMMENDED STEEL SUPPI 8. DIMENSIONS LISTED AS FOLLO ENGLISH FT-IN METRIC [mm]	READ HREAD WELDING LUDE DRY DRAWINGS ([344 kPa] DO NOT USE DNNECTING DLES. REFER TO ORT DRAWING.)		Ē	FACE B PLAN VIEW		FACE D
1'-9 3/8" [543] (M) 3'-11 3/4" [1213] (a) 4" [100] BFW O 1'-11 1/8" [587] 2'-0.3 [61] 6'-10.7 [210] 6'-11.3 [212] 7'-4 [223]	FLUID N (4) # [1	(2) 2" [50] MPT MAKE-UP (2) 2" [50] MPT DRAIN	1'-10 7/8" [581] 2'-11 3/8" [899] (M) 6'-5 1/8" [1959] 14'-10 3/4" [5 1/4" [133] 5'-6 1/4" [1683] -1'-3" [381] (2) 3" [80] MPT OVERFLOW	4539]	1'-2" [(4) 1/2" [15] FPT VENT 1'-5 1/8" [435]	ACCESS COOR COOR COOR COOR COOR COOR COOR CO	
					FACE A		
SHIPPING WEIGHT 31220 lbs+ [14165]	kg+ OPE WI	RATING EIGHT	43820 lbs+ [19880] kg+	HEAVIEST SECTION WEIGHT	N 13420 lbs+ [6090	0] kg+ NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG