NOTES  NO	UNIT	CLOSED CIRCUIT COOLER		EVADOO TNA		Clevapco		WG. # WB3TM1808-D	DRC-SF REV
LIGHT STANDARD LOCATION  LIGHT STANDARD STANDARD SECTION  FACE D  FACE	MODEL #	ATWB 10-4I18-Z	SCALE NTS	T EVAPO	O, IN	C.	SE	ERIAL #	DATE <sub>11/25/2025</sub>
(2) 4" [100] BFW (1448) ** (1772) ** (2) 4" [100] BFW (1448) ** (1772) ** (2) 4" [100] BFW (1448) ** (1541	2. HÉAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DE! 4. +UNIT' ACCES 5. MAKE-I 20 psi M 6. *-APPR FOR PI PIPING 7. SERIES DRAIN 8. 3/4" [19 RECOM 9. DIMEN E	EST SECTION IS UPPER SECENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUE SORIES (SEE ACCESSORY UP WATER PRESSURE WIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONN S S FLOW PIPING AND AUX. C BY OTHERS.  29MM] DIA. MOUNTING HOLES WIMENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS NGLISH FT-IN	DE DE DRAWINGS)  44 kPa] NOT USE ECTING  CROSSOVER S. REFER TO DRAWING.	7" [ 178]	PLAN	VIEW		ACCESS DOOR	FACE D
SHIPPING 20420 lbs+ [9265] kg+ OPERATING 32690 lbs+ [14830] kg+ HEAVIEST SECTION 16770 lbs+ [7610] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TI M	F	2'-63/4" * [781]  2"[50] MPT MAKE-UP  3 5/8"  3 5/8"  3 5/8"  3 5/8"  3 5/8"  4 1/4" [108]  5'-113 [182]	3/4" ————————————————————————————————————	9'-1/8" [2748] FLUID OUT  14'-2 3/ [4328]  6"  5'-2 1/4"  [1580]	AUX. CROSSO	(2) 1/2" [15] FPT VENT  LOW PIPING SEE NOTE 7)  OVER DRAIN SEE NOTE 7)		18'-0" [ 5486]	
WEIGHT 20420 lb3+ [4200] kg+ WEIGHT 32030 lb3+ [14000] kg+ WEIGHT 10770 lb3+ [7010] kg+ 2 1 Li4	SHIPPING WEIGHT	20420 lhs+ [92	265] ka+	OPERATING 32690 lbs+ [148:	301 kg+		16770 lbs+ [7610] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: TLM