UNIT	CLOSED CIRCUIT COOLER	
MODEL #	LSWE 8P-7O24	SCALE NTS




DWG. # WLEP82414-DRD-ST REV. SERIAL # DATE_{12/14/2025}

FACE D

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

FACE C



3'-8 7/8" * (4) 4" [100] BFW FLUID IN (4) 1/2" [15] (4) 1/2" [15] FPT VENT **FPT VENT** 3'-11 3/4" * [1213] (4) 4" [100] BFW 6'-1/2" [1842] FLUID OUT 13'-3 7/8" [4061] 2" [50] MPT MAKE-UP (2) ACCESS DOOR 7'-3 3/8" (2) 3" [80] MPT **ÖVERFLOW** 2'-11 7/8" [911] 3 1/8" [79] 10" [254] 1'-5" [432] 24'-1" [7341] 3'-2 5/8" [981] **FACE A** 3'-8 3/8" [1127] 2" [50] MPT DRAIN 7'-10" [2388]

FACE B