


UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-LRWB 3-2D6

DWG. #	WV030604-DRC-ST	REV.	-
SERIAL #		DATE	2/22/2026

NOTES:
1. (M) - FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
6. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

PLAN VIEW



SHIPPING
WEIGHT

2420 lbs+ [1100] kg+

OPERATING
WEIGHT

3650 lbs+ [1660] kg+


HEAVIEST SECTION
WEIGHT

2420 lbs+ [1100] kg+


NO. OF SHIPPING SECTIONS
1

DRAWN BY:
TLS

FACE C



FACE D



FACE A