UNIT CLOSED CIRCUIT COOLEI	R	EVADCO TI	VIC EVO	apco	DWG. # WV080908-DRD-ST	REV.
MODEL # eco-LRWB 8-4M9	CALE NTS	EVAPCO, II	VC.	9	SERIAL #	DATE 1/26/2025
6. * - APPROXIMATE DIMENSIONS DO NO USE FOR PRE-FABRICATION OF CONN 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] M/	AWINGS) EFER TO AWING NGLISH FT IN METRIC] [mm] DT NECTING PIPING AX	FACE B PLAN VIEW		FACE C 15'-2.1 [462!		FACE D
	S" * -	• •			[6'-3"	-
(2) 4" [100] BFW FLUID IN		4'-6 3/4"	(2) 1/2" [15] FPT VENT			
(2) 4" [100] BFW FLUID OUT	2'-3" [686]	7'-7" [2311]				6'-7 3/4" [2026]
3 1/4" TYP		7"		ACCESS DOOR		
3" [80] MPT OVERFLOW	4 1/4" 2 5/6	/8"	-	8'-5 3/8" [2575]	2" [50] MPT MAKE-UP	ACCESS DOOR
2" [50] MPT	2'-10"	1'-3 7/8" [405]		15'-2 1 [4629	1/4" 9]	DOOK
FACE A FACE B						
SHIPPING 10380 lbs+ [4710] kg+ WEIGHT	OPERATING WEIGHT	15430 lbs+ [7000] kg+	HEAVIEST SECTION WEIGHT	10380 lbs+ [4710] kg+	NO. OF SHIPPING SECTIONS 1	DRAWN BY: TLS