UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 7-7J9-Z	SCALE NTS



DWG. # REV. CW4C070914-DRA-SF DATE_{12/13/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

1'-9 3/8' [543]

(2) 4" [100] BFW FLUID IN


2" [50] MPT


2" [50] MPT DRAIN

1'-11 1/8" [587]

MAKE-UP







7'-4" [2235 **FACE B**

3'-6 1/4' [1073]

1'-10 7/8" [581]

(2) 4" [100] BFW FLUID OUT

1'-3" [381]

5 1/4" * [133]

3" [80] MPT OVERFLOW

6'-5 1/8" [1959]

4'-3 7/8" [1318]