UNIT CLOSED CIRCUIT COOLER				DCO T		apeo °	DWG. #	WV030606-DRD-SF	REV.
MODEL # eco-l	LRWB 3-3H6-Z	SCALE NTS	T EVA	APCO, I	NC.		SERIAL #		DATE _{11/26/2025}
FPT DENOTES BFW DENOTES GVD DENOTES FLG DENOTES PE DENOTES 3. +UNIT WEIGH ACCESSORIES 4. 3/4" [19mm] DI. RECOMMENDI 5. DIMENSIONS I 6. * - APPROXIMA USE FOR PRE- CONNECTING 7. MAKE-UP WAT 20 psi [137 kPa	S MALE PIPE THREAD S FEMALE PIPE THREAD S BEVELED FOR WELDI S GROOVED S FLANGE PLAIN END T DOES NOT INCLUDE S (SEE ACCESSORY DR A. MOUNTING HOLES. F ED STEEL SUPPORT DR LISTED AS FOLLOWS: E [IATE DIMENSIONS DO NO F-FABRICATION OF PIPING. TER PRESSURE J] MIN, 50 psi [344 kPa] M PIPING AND AUX. CRO	AWINGS) REFER TO RAWING RIGHT IN METRIC] [mm] OT	PLAN VIEW	2-4 1/2" 1029]		FACE C 10'-1 7/8 1 3096 FACE A	8"		FACE D
11 1/4" * - [286] * - (2) 4" [100] BFF FLUID (2) 4" [100] BFV FLUID OUT 3 1/4" TYP 2" [50] MP OVERFLOW 2" [50] MP DRAII	W N N N N N N N N N N N N N N N N N N N		3'-7 1/2" [1106] 1/2" * [1106] 6'-7 3/ [2026] 5 1/4" * [919] 8 3/4" [919] 2 5/8" [67] 6 5/8" [167]	4" 1'-1 1/8" 1'-1 1/8"	(2) 1/2" [15] FPT VENT SERIES FLOW PIPII (BY OTHERS) AUX. CROSSON (BY OTHERS) ACCESS DOOR		1" [25] MAKE-	ACCESS DOOR DOOR IMPT UP	5'-3 3/8" [1610]
SHIPPING	2910 lbs+ [1320] k	(g+	OPERATING 4240) lbs+ [1925] kg+	HEAVIEST SECTION	2910 lbs+ [1320] kg+	NO. OF S	HIPPING SECTIONS 1	DRAWN BY:
WEIGHT		·	WEIGHT	r1 .a.	WEIGHT			•	