NIT CLOSED CIRCUIT COOLER			TNIC	evapco	DWG. # WLE041210-DRD-ST	REV.	
10DEL #	eco-LSWE 4-5J12	SCALE NTS	EVAPCO,	TINC.		SERIAL #	DATE <sub>11/27/2025</sub>
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DI FLG DE PE DEN 4. +UNIT \ ACCES 5. 3/4" [19 RECON 6. DIMEN: 7. * - APP USE FC 8. MAKE-I 20 psi 9. MAKE-I	N MOTOR LOCATION EST SECTION IS COIL SECT ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUD SORIES (SEE ACCESSORY IMMIDIAL MOUNTING HOLE MENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS ROXIMATE DIMENSIONS DO DR PRE-FABRICATION OF C UP WATER PRESSURE 137 KPa] MIN, 50 psi [344 KPa] UP CONNECTION LOCATED CONNECTION END OF UNIT	D EAD EAD ELDING  DE DRAWINGS) S. REFER TO TORAWING S: ENGLISH FT IN [METRIC] [mm] D NOT ONNECTING PIPING A] MAX T-5/8" [194]		4'-3/4" [ 1238 ]	FACE C	1 3/4"	FACE D
2' (	4" [100] BFW FLUID IN  4" [100] BFW FLUID OUT  (2) ACCESS DOOR 1" [25] MPT MAKE-UP  1'-7 5/8" 498 ]  1'-8 7/8" 530 ]	4'-3/4" [1238] FACE B	2'-10 1/2" * 5'-1" [ 877 ] * [ 1549 ]  2" [50] FPT	8'-8 1/2" [ 2654 ] 1'-5" 432 ]	1/2" [15] FPT VENT  11'-11 [ 36 FACE A	13/4"	
SHIPPING WEIGHT	7730 lbs+ [351		ERATING 10210 lbs+ [4635] kg+	HEAVIEST SE WEIGH	CTION 5620 lbs+ [2550] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: