UNIT CLOSED CIRCUIT COOLER			EVAD.	CO TI	NC eva	pco	WG. # WLE051806-DRD-ST	REV.
MODEL # eco-LSV	/E 5-3L18	NTS	EVAP	CO, II	NC. eva	SE	ERIAL #	DATE <sub>11/27/2025</sub>
3. MPT DENOTES M FPT DENOTES FE BFW DENOTES B GVD DENOTES G FLG DENOTES FL PE DENOTES PL 4. +UNIT WEIGHT D ACCESSORIES (S 5. 3/4" [19mm] DIA. M RECOMMENDED 6. DIMENSIONS LIST 7. * - APPROXIMATE USE FOR PRE-FA 8. MAKE-UP WATER 20 psi [137 kPa] M	ON IS COIL SECTION ALE PIPE THREAD MALE PIPE THREAD MALE PIPE THREAD EVELED FOR WELDING ROOVED ANGE IN END DES NOT INCLUDE EE ACCESSORY DRAWIN IOUNTING HOLES. REFER STEEL SUPPORT DRAWIN TED AS FOLLOWS: ENGLIS [METR DIMENSIONS DO NOT BRICATION OF CONNECT PRESSURE N, 50 psi [344 kPa] MAX	R TO NG SH FT IN RIC] [mm]	FACE I PLAN VIEW	_		FACE C  17'-11 7/ [ 5483 ]  FACE A		FACE D
4" [100] BI FLUID  4" [100] BF FLUID O  (2) ACCESS DOOI  2" [50] FPT OVERFLOW  2'-2 3/4"  [ 679 ]  1 2'-5"  [ 737 ]  2'-7 7/8"  [ 810 ]  2'-8 3/8"  [ 822 ]	JT	<u> </u>	4 3/4" * [119] *  L-1/2" [40] MPT MAKE-UP  5'-1 1/8" [1553]  3 1/8" [79]  1'-7 1/4" [489]  -2" [50] MPT DRAIN  1'-10" [559]	9'-2 1/8" [ 2797 ]	1/2" [15] FPT VENT	17'-11 7/ [ 5483 ]  FACE A	8"	DRAWN BY:
SHIPPING WEIGHT	11560 lbs+ [5245] kg+	OP V	PERATING 16550 lbs+ [7 WEIGHT	7510] kg+	HEAVIEST SECTION WEIGHT	7590 lbs+ [3445] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: TLS