UNIT ED CIRCUIT CC	EVADOO T	NC evapeo	wg. # WV051214-DRD-ST	REV.
MODEL # LRWB 5-7L12 SCALE NTS	EVAPCO, I	NC.	ERIAL #	DATE 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT II [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIF 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	DI AN VIEW	FACE C		FACE D
		18'-2 5/8" [5553] <u>FACE A</u>	-	
- - 2'-6 3/8" * -				
4" [100] BFW FLUID IN	1/ FI	2" [15] PT VENT	[1905]	
4" [100] BFW — 3'-11 [12	3/4" * [1849]	ACCESS		6'-7 3/4" [2026]
[83'] TYP	3'-1/4"	DOOR		1'-8 1/8" [511]
OVERFLOW 2" [50] MPT 2" [53] 1-8 7/8"	2.5/8"	11'-5 3/4" [3499] 18'-2 5/8" [5553]	1" [25] MPT MAKE-UP	ACCESS
DRAIN 5'-5/8" [1540]	[346]	[5553] FACE A		
SHIPPING 40 lbs+ [4600] WEIGHT	OPERATING)30 lbs+ [7275] k	HEAVIEST SECTION 40 lbs+ [4600] WEIGHT	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS