NIT	CLOSED CIRCUIT C	OOLER	FV/A DCO	TNIC	evanço	DWG. #	WV080906-DRD-ST	REV.
IODEL #	LRWB 8-3J9	SCALE NTS	EVAPCO,	TIC.		SERIAL #		DATE 11/5/2025
2. MPT DE FPT DE BFW DE GVD DE FLG DE PE DEN 3. +UNIT V ACCES: 4. 3/4" [19i RECOM 5. DIMENS 6. * - APPF USE FO 7. MAKE-U	N MOTOR LOCATION NOTES MALE PIPE THRE NOTES FEMALE PIPE TH ENOTES BEVELED FOR W NOTES FLANGE OTES PLAIN END VEIGHT DOES NOT INCLUS SORIES (SEE ACCESSOR mm] DIA. MOUNTING HOL MENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ROXIMATE DIMENSIONS I R PRE-FABRICATION OF IP WATER PRESSURE 37 kPa] MIN, 50 psi [344 k	READ VELDING UDE RY DRAWINGS) LES. REFER TO RT DRAWING WS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPING	FACE B PLAN VIEW	7'-10"	FACI	'-2 1/4" 4629]		FACE D
2'- [6	1/2" * - 3	'-8 7/8" * - 1140]					[1905]	
(2) 4" [10 FI	0] BFW LUID IN		3'-11 1/4"		(2) 1/2" [15] FPT VENT			
(2) 4" [10 FLU	0] BFW OUT		3'-11 1/4" ['-7 1/2" * [1202] [495] * 6'-11 1/2" [2121]		ACCESS —			6'-7 3/4" [2026]
3 1/4 [83]	ТҮР	M.	7" * [178] * 3'-1/4" [919]		DOOR			
3" [80 OVER	n] MPT FLOW	4 1/4"	2 5/8"		8'-5 3/8" [2575]		1'-8 1/8" [511] – 2" [50] MPT MAKE-UP	ACCESS DOOR
2" [5		7'-10" [2388]		1'-3 7/8"	15 FACE	'-2 1/4" 4629] E A		
SHIPPING WEIGHT	7430 lbs+ [33	Lorenz	TING 12090 lbs+ [5485] kg+	HEAVIEST SE WEIGH	CTION 7430 lbs+ [3375] kg+	NO. OF	SHIPPING SECTIONS 1	DRAWN BY: TLS