UNIT	CLOSED CIRCUIT COOLER	
MODEL #	LRWB 5-3K9-Z	SCALE NTS

EVAPCO, INC. evapeo

DWG. # WV050906-DRD-SF REV. SERIAL # DATE 11/5/2025

NO. OF SHIPPING SECTIONS

DRAWN BY:

NOTES:

SHIPPING

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN $[{\sf METRIC}]$ [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
- 7. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER
- SERIES FLOW PIPING AND AUX. CROSSOVEF DRAIN ARE BY OTHERS


OPERATING

WEIGHT

8440 lbs+ [3830] kg+

5050 lbs+ [2295] kg+





HEAVIEST SECTION

WEIGHT

5050 lbs+ [2295] kg+