UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 10-4L36	SCALE NTS



DWG. # REV. WLETM3608-DRD-ST DATE_{11/26/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED FLG DENOTES FLANGE

- PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

FACE C





