




UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 4-3H6-Z	SCALE NTS

NOTES:  
 1. (M)- FAN MOTOR LOCATION  
 2. MPT DENOTES MALE PIPE THREAD  
 FPT DENOTES FEMALE PIPE THREAD  
 BFW DENOTES BEVELED FOR WELDING  
 GVD DENOTES GROOVED  
 FLG DENOTES FLANGE  
 PE DENOTES PLAIN END  
 3. +UNIT WEIGHT DOES NOT INCLUDE  
 ACCESSORIES (SEE ACCESSORY DRAWINGS)  
 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
 RECOMMENDED STEEL SUPPORT DRAWING  
 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN  
 [METRIC] [mm]  
 6. \* - APPROXIMATE DIMENSIONS DO NOT  
 USE FOR PRE-FABRICATION OF CONNECTING PIPING  
 7. HEAVIEST SECTION IS COIL SECTION  
 8. MAKE-UP WATER PRESSURE  
 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX  
 9. MAKE-UP CONNECTION LOCATED 7-5/8" [194]  
 FROM CONNECTION END OF UNIT  
 10. SERIES FLOW PIPING AND AUX. CROSSOVER  
 DRAIN ARE BY OTHERS



**FACE D**



**FACE B**

**FACE A**