CLOSED CIRCUIT COOLER			EVA DOC	TNIC	eva) D\	DWG. # WLE041208-DRD-SF		REV.
10DEL #	eco-LSWE 4-4l12-Z	SCALE NTS	EVAPCO), INC.		SE	ERIAL #		DATE _{11/27/2025}
2. MPT I FPT D BFW I GVD I FLG PE DE 3. +UNIT ACCE 4. 3/4" [1 RECO 5. DIMEI 6. * - API USE F 7. HEAV 8. MAKE 20 MSE FROM 10. SERI	AN MOTOR LOCATION DENOTES MALE PIPE THRE. ENOTES FEMALE PIPE THE DENOTES BEVELED FOR W DENOTES GROOVED SENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SECONOMINATION OF SECONOMINATE DIMENSIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS DEST SECTION IS COIL SECONOMINATE PRESSURE [137 KPa] MIN, 50 psi [344 KF-UP CONNECTION END OF UNI ES FLOW PIPING AND AUX N ARE BY OTHERS	READ ELDING DE Y DRAWINGS) ES. REFER TO T DRAWING YS: ENGLISH FT I [METRIC] [mn O NOT CONNECTING PIF TION Pa] MAX D 7-5/8" [194] T	PLAN VIEW			FACE C 11'-11 3/ [3651/	4"	-	FACE D
	1'-1/8" * [308] * (2) 4" [100] BFW FLUID IN SERIES FLOW PIPING (BY OTHERS) (2) 4" [100] BFW FLUID OUT 2) ACCESS DOOR 1" [25] MPT MAKE-UP 2'-2 1/8" [664]		1'-8" * 2'-3" * [687] * 2'' [50] FPT OVERFLOW 3'-7 1/2" [1105] 1'-6 7/8" [479]	8'-1" [2464]	AUX. CROSDRAIN (BY	SSOVER			
	1'-7 5/8" —— [498] 1'-8 7/8" ——	4'-3/4" [1238]	3 1/8" [79] -2" [50] MPT DRAIN 1'-7" [483]	1'-5" [432]	•	11'-11 3/ [3651 FACE A	/4 "		
SHIPPING WEIGHT	6710 lbs+ [30	FACE 145] kg+	OPERATING 8960 lbs+ [4065] kg+ weight	HEAVIEST SI WEIGH	ECTION IT	4720 lbs+ [2145] kg+	NO. OF SHIPPING SECTION	DNS 2	DRAWN BY: