

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-LRWB 5-4H6

DWG. #	WV050608-DRC-ST	REV.	-
SERIAL #		DATE	2/1/2026

NOTES:  
1. (M)- FAN MOTOR LOCATION  
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END  
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)  
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING  
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN  
[METRIC] [mm]  
6. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING  
7. MAKE-UP WATER PRESSURE  
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

