UNIT CLOSED CIRCUIT COOLER	EVADOO TNIC EVELDED	vg. # WV050908-DRC-ST	REV.
MODEL # eco-LRWB 5-4I9 SCALE NTS	EVAPCO, INC. evapco	RIAL #	DATE <sub>11/26/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]  6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIP  7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	FACE B. 5'-5/8"		FACE D
- <del>-</del> 2'-6 3/8" *   <del>-</del>	15'-2 1/4" [ 4629 ]  FACE A	6'-3" [ 1905 ]	
4" [100] BFW FLUID IN  4" [100] BFW FLUID OUT  3 1/4" TYP.	2'-3" * [1297]  2'-3" * [1297]		6'-7 3/4" [ 2026 ]
3" [80] MPT OVERFLOW  2" [50] MPT	2 5/8"	-1" [25] MPT MAKE-UP	1'-8 1/8" [ 511 ] ACCESS DOOR
SHIPPING 6700 lbs+ [3040] kg+	DPERATING 10330 lbs+ [4690] kg+ HEAVIEST SECTION 6700 lbs+ [3040] kg+ WEIGHT	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS