

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 9-5K21


**EVAPCO, INC.** 

DWG. #	WB3092110-DRC-ST	REV.	-
SERIAL #		DATE	2/1/2026

NOTES:


- (M) FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN  
METRIC [mm]



**FACE B**

**PLAN VIEW**



**FACE C**


**ACCESS DOOR**

**ACCESS DOOR**

**FACE D**

**FACE A**

**FACE B**



**FACE A**