

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 9-6L21


EVAPCO, INC. 

DWG. #	WB3092112-DRC-ST	REV.	-
SERIAL #		DATE	1/31/2026


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING
WEIGHT

32490 lbs+ [14740] kg+

OPERATING
WEIGHT

45070 lbs+ [20445] kg+

HEAVIEST SECTION
WEIGHT

29390 lbs+ [13335] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:
SLR