

UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WLETM1806-DRD-ST	REV.
MODEL #	eco-LSWE 10-3M18	SCALE NTS		SERIAL #		DATE 1/31/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
4. BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
8. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX




DWG. # WLETM1806.DBD ST

SERIAL #

REV.



DATE 1/31/2026

FACE C



FACE B

PLAN VIEW



FACE B

SHIPPING WEIGHT 22110 lbs+ [10030] kg+ OPERATING WEIGHT 31860 lbs+ [14455] kg+ HEAVIEST SECTION WEIGHT 14820 lbs+ [6725] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TLS