






UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 		DWG. # WLE040606-DRD-SF		REV. -											
MODEL # eco-LSWE 4-3F6-Z		SCALE NTS				SERIAL #		DATE 8/29/2025											
<div><div><div>NOTES:</div><div><div>1. (M)- FAN MOTOR LOCATION</div><div>2. MPT DENOTES MALE PIPE THREAD</div><div>FPT DENOTES FEMALE PIPE THREAD</div><div>BFW DENOTES BEVELED FOR WELDING</div><div>GVD DENOTES GROOVED</div><div>FLG DENOTES FLANGE</div><div>PE DENOTES PLAIN END</div><div>3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div><div>4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING</div><div>5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]</div><div>6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div><div>7. HEAVIEST SECTION IS COIL SECTION</div><div>8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX</div><div>9. MAKE-UP CONNECTION LOCATED 7-5/8" [194] FROM CONNECTION END OF UNIT</div><div>10. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS</div></div></div><div><div><div><div><div>FACE B</div><div>PLAN VIEW</div></div><div></div></div><div><div><div>FACE C</div><div></div></div><div><div><div>FACE D</div><div></div></div><div><div><div>FACE A</div><div></div></div></div></div><table><tr><td>SHIPPING WEIGHT</td><td>3120 lbs+ [1420] kg+</td><td>OPERATING WEIGHT</td><td>4170 lbs+ [1895] kg+</td><td>HEAVIEST SECTION WEIGHT</td><td>1990 lbs+ [905] kg+</td><td>NO. OF SHIPPING SECTIONS</td><td>2</td><td>DRAWN BY:</td><td>TLS</td></tr></table></div></div></div></div>										SHIPPING WEIGHT	3120 lbs+ [1420] kg+	OPERATING WEIGHT	4170 lbs+ [1895] kg+	HEAVIEST SECTION WEIGHT	1990 lbs+ [905] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	TLS
SHIPPING WEIGHT	3120 lbs+ [1420] kg+	OPERATING WEIGHT	4170 lbs+ [1895] kg+	HEAVIEST SECTION WEIGHT	1990 lbs+ [905] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	TLS										