

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-6N14	SCALE NTS


EVAPCO, INC.

DWG. #	WB3121412-DRC-ST	REV.	-
SERIAL #		DATE	2/17/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

HEAVIEST SECTION WEIGHT

SHIPPING
WEIGHT

30860 lbs+ [14000] kg+

**OPERATING
WEIGHT**

43780 lbs+ [19860] kg+

HEAVIEST SECTION WEIGHT

37800 lbs + [13610] kg +

NO. OF SHIPPING SECTIONS

2

DRAWN BY: SLD