UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-5J8

EVAPCO, INC. Evapeo




DWG. # REV. WB3090810-DRC-ST DATE_{12/14/2025} SERIAL #


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





FACE A





DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 10910 lbs+ [4950] kg+ 15090 lbs+ [6845] kg+ 9610 lbs+ [4360] kg+ WEIGHT WEIGHT WEIGHT