INIT CLOSED CIRCUIT COOLER			EVAPCO, INC. Evapeo			DWG. # WB3241408-DRC	-ST REV
IODEL #	eco-ATWB 24-4M14	SCALE NTS	EVAPCO,	INC.	Value	SERIAL #	DATE <sub>11/21/2025</sub>
2. HEAV 3. MPT I FPT I BFW I GVD I FLG I PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APP FORN 7. 3/4" [1 RECC	AN MOTOR LOCATION PIEST SECTION IS UPPER SIDENOTES MALE PIPE THRE DENOTES FEMALE PIPE THE DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END PUBLISHED SOR SOR SEE ACCESSOR ENOTES (SEE ACCESSOR HIN (137 KPa), 50 psi MAX (SECOMMATE DIMENSIONS DOPRE-FABRICATION OF CON	AD READ FELDING  JDE Y DRAWINGS)  344 KPa] D NOT USE NECTING  ES. REFER TO RT DRAWING.			FACE B PLAN VIEW	FACE C  (2) ACCESS DOOR  FACE A	FACE D
				7" [ 178]	1'-3 1/4" [ 387 ]		
	2-6-3/4 * (4) 4" [7	(2) 2" [50] MPT DRAIN	(4) 4" [100] BFW (4) 4" [100] BFW (5) [1759] * [	9'-1/8'' [ 2748]	(4) 1/2" [15] FPT VENT 3/8"		
	OVERFLOW	5 1/8" [ 130] - 24	11'-10" [ 3607 ]		1'-6 1/2" [ 470 ]	13'-11 3/4"	
			CE B			FACE A	

HEAVIEST SECTION WEIGHT

20100 lbs+ [9120] kg+

SHIPPING WEIGHT OPERATING WEIGHT

68380 lbs+ [31020] kg+

46320 lbs+ [21015] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS