
| UNIT    | CLOSED CIRCUIT COOLER |           |
|---------|-----------------------|-----------|
| MODEL # | eco-ATWB 9-6L21       | SCALE NTS |


EVAPCO, INC. Evapco


DWG. # WB3092112-DRC-ST REV. SERIAL # DATE<sub>12/14/2025</sub>

## NOTES

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]







SHIPPING WEIGHT 32490 lbs+ [14740] kg+

OPERATING WEIGHT

45070 lbs+ [20445] kg+

HEAVIEST SECTION WEIGHT

29390 lbs+ [13335] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR